

Sciencetech 2803 provides an extensive hands on learning on Delta, Adaptive Delta, Sigma Delta Modulator & Demodulator.

Features

- Modulator and Demodulator on same board
- On-board DDS Signal Generator for standard and Arbitrary signals
- Selectable Sampling Frequencies
- On board Transmission effect
- Selectable step size for Integrator
- Detailed study of granular noise and slope overloading
- On board 2nd order Butterworth Low Pass filter
- SMD LED Indicators
- Can be issued just like a book for hands-on learning

Scope of Learning (Experimentation)

Delta Modulator & Demodulator

Study and analysis of:

- Delta Modulation and Demodulation.
- Sample & Hold output by varying the Sampling as well as Signal frequency.
- Integrator output at the Modulator by varying the Sampling frequency.
- Improved Integrator output by varying the gain control frequency.
- Slope Overload distortion problem.
- Granular Noise problem.
- Single bit Delta modulated PCM output.
- Integrator output at the Demodulator.
- Analyze the final Delta demodulated output with Second order Low Pass Butterworth filter .

Adaptive Delta Modulator & Demodulator

- Adaptive Delta Modulation.
- Single bit PCM output by varying the Sampling frequency.
- Variable step register at the Modulator side.
- Accumulator and Add/Subtract at the Modulator side.
- Accumulator and Add/Subtract at the Demodulator side.
- Overcoming of Slope Overload distortion occurred in Delta Modulation by the generation of variable step size.
- Analyze the final Adaptive Delta demodulated output with Second order Low Pass Butterworth filter.

Sigma Delta First Order

- Sigma Delta Modulation of the First order.
- Sigma output after the summation of two signals.
- Integrator output by varying the Sampling frequency.
- Single bit PCM output at the Sigma Delta Modulator.
- Sigma Delta Demodulation of First order.
- Decimator filter output at the Demodulator by varying the position of the clock enable switch.
- Analyze the final Sigma Delta Demodulation output with Second order Low Pass Butterworth filter at the given test point.

Sigma Delta Second Order

- Sigma Delta Modulation of Second order.
- First order Sigma output .
- Second order Sigma output.
- Integrator output by varying the Sampling frequency.
- Single bit PCM output at the Sigma Delta Modulator.
- Sigma Delta Demodulation of Second order.
- Decimator filter output at the Demodulator by varying the position of the clock enable switch.
- Analyze the final Sigma Delta Demodulation of Second order output with Second order Low Pass Butterworth filter.

Transmission effects



- Attenuator effect.
- Filter effect.
- Noise effect by varying the noise level.

Simtel 11 - Digital Communication Interactive Software (optional)

Topics

- Source: Signal Source, Pulse Generator, Data Generator, Delay
- Math Operations: Adder, Subtractor, Multiplier
- Natural and Flatop Sampling
- Line Encoding and Decoding
- Adaptive Modulator and Demodulator

For more details refer Simtel 11 Catalog



Technical Specifications

Modulation & Demodulation

Techniques : Delta
: Adaptive Delta
: Sigma Delta First order
: Sigma Delta Second order

Internal Signal Generator: Direct Digital Synthesizer

Types of Signal : Sine, Square, Triangle, Arbitrary signals

Frequency : 500Hz, 1KHz, 2KHz, 3KHz

External Signal

Types of Signal : Sine, Square, Triangle, Arbitrary signals

Maximum Input Voltage : 3Vpp (Max.) +1.5V DC offset

Frequency : 500Hz to 3.5KHz

SMD LED Indicators : 48 nos for

DDS signal selection

DDS signal frequency selection

Sampling selection

Technique selection

Interconnect path

Transmission Effect : Attenuation (7dB & 10dB)

Noise

Filter

Crystal Frequency : 8MHz

Sampling Frequencies : 16KHz, 32KHz, 64KHz, 128KHz, 256KHz

Integrator step : Normal & 3 times

Selection Mode : Push switches

Number of Test Points : 46 nos

Low Pass Filter : Cut-off frequency-5KHz

Digital Filter : Decimation filter (16:1)

Product Tutorial : Online on www.SciencetechLearning.com

Dimensions (mm) : W 326 x D 252 x H 52

Power Supply : 110V - 260V AC, 50/60Hz

Weight : 1.5Kg (Approximately)

Operating Conditions : 0-40°C, 85% RH

Included accessories : 2mm Patch cord - 2nos